PRODUCT SPECIFICATIONS

Product: Idealine Pfix

Description

Idealine Pfix (Phoototooling Fixer) is a Rapid Fixer based on AmmoniumThiosulfate in an Acid solution.

Applications.

Used for fixing of Phototooling films.

Compatible films in Pfix.

Idealine RPF, OPF, CPF and DPF, Vivaldi VGB7-2 and VR7-2 are fully compatible with Vfix.

Preparation and start.

Processor: Dilute the chemistry with 4 parts of water, fill the processor.

Replenisher tank: Dilute the chemistry with 4 parts of water, mix well and fill the replenisher tank.

Parameters for the processor

	Rapiline & AgfaRap	AgfaLine
Developing time	30 s	35 s
Developing temperature	30-35 °C	30-32 °C
Repl. rate without silver recovery	500 ml/m ² - 50 % black	500 ml/m ² - 50 % black
Repl. rate with silver recovery	125 ml/m ² - 50 % black	125 ml/m ² - 50 % black

Monitoring Pfix.

Pfix is a stable chemistry. Once up and running, and correctly replenished, monitoring is hardly required.

Storage conditions

Always store Vdev in a frost-free environment. Precipitation will result if the chemistry is frozen.

Shelf life

36 months after manufacturing.

Precautions

Avoid contact with skin. After contact, rinse thoroughly with water;

Sales packaging.

ABC code: ESG2N

Description: Pfix 4x5/100 Packaging: 4 x 5 l.

